



250/25 kN Compression Frame with Platens

Code: [39-6120](#)

Product Group: [ADR 250/25 Compression Frames](#)

- Open sided for ease of specimen loading
- Meets EN 12390-5, 1521, 13161, 772-6 and ASTM C78 for standard section beams
- Optional ball seating assembly

This rigidly constructed, open sided frame is suitable for testing 100 mm and 150 mm square-section beams. The frame supports a hydraulic ram and upper sub-platen assembly incorporating a spherical seating. The upper and lower sub-platens will accept various specimen loading bearers, which are supplied separately.

Further Information

****Not available for sale in the USA****

Accessories



100 kN Flexural Fitting Kit ADR Auto for 110 - 120 V AC, 60 Hz, 1 ph

Code: [37-6135/02](#)



100 kN Flexural Fitting Kit ADR Auto for 220 - 240 V AC, 60 Hz, 1 ph

Code: [37-6135/06](#)



100kN Flexural Fitting Kit (ADR) Used for Connecting Flexural Frames to ADR Compression Machines.

Code: [37-6138](#)



ASTM C78 Specimen Bearer Assembly Case-Hardened 38mm Dia X 160mm Length.

Code: [37-6132](#)



Ball Seating Assembly 150mm Dia Platens.

Code: [37-6133](#)



BS 1881 Specimen Bearer Assembly 38mm Dia X 160mm Length.

Code: [37-6131](#)



Change over valve assembly kit for 230V, 50/60Hz

Code: [37-0011/01](#)



Standard Distance Piece - 100 mm Depth

Code: [37-5100](#)



Standard Distance Piece - 20 mm Depth

Code: [37-4980](#)



Standard Distance Piece - 50 mm Depth

Code: [37-5000](#)



Standard Distance Piece - 60 mm Depth

Code: [37-5020](#)



Standard Distance Piece - 80 mm Depth

Code: [37-5050](#)

Alternatives



Accu-Tek Touch 250 Automatic Compression Machine 110 V 60Hz

Code: [36-1690/02](#)



Accu-Tek Touch 250 Automatic Compression Machine 220-240 V 50Hz

Code: [36-1690/01](#)



Accu-Tek Touch 250 Automatic Compression Machine 220-240 V 60Hz

Code: [36-1690/06](#)



ADR Touch Manual Power Pack Including Fitting Kit 110V 60Hz 1Ph

Code: [36-6165/02](#)



ADR Touch Manual Power Pack Including Fitting Kit 220-240V 50/60Hz 1Ph

Code: [36-6165/01](#)