

Soundness of Aggregates



Wire Basket - 150 µm wire mesh

Code: [81-4819](#)

Attributes: [Description](#) = Wire Basket - 150 µm wire mesh, [Aperture Size](#) = 150 µm

Standards:



Wire Basket - 600 µm wire mesh

Code: [81-4821](#)

Attributes: [Description](#) = Wire Basket - 600 µm wire mesh, [Aperture Size](#) = 600 µm

Standards:



Wire Basket - 1.18 mm wire mesh

Code: [81-4823](#)

Attributes: [Description](#) = Wire Basket - 1.18 mm wire mesh, [Aperture Size](#) = 1.18 mm

Standards:



Wire Basket - 3.35 mm wire mesh

Code: [81-4825](#)

Attributes: [Description](#) = Wire Basket - 3.35 mm wire mesh, [Aperture Size](#) = 3.35 mm

Standards:



Hydrometer

Code: [82-3505](#)

Attributes: [Description](#) = Hydrometer used with sodium sulphate method

Standards: [BS 812](#), [EN 1367-2](#), [ASTM C88](#), [AASHTO T104](#), [BS 7188](#)



Hydrometer

Code: [82-3510](#)

Attributes: [Description](#) = Hydrometer used with magnesium sulphate method

Standards: [BS 812](#), [EN 1367-2](#), [ASTM C88](#), [AASHTO T104](#)