



IF IT'S WORTH BUILDING, IT'S WORTH TESTING

Contents

www.ele.com
+44 (0) 01525 249 200



This wishlist was generated on 06/04/2018, and contains the following Products:

78-1245

Dial Thermometer

78-5447/01

Electronic Balance - 3600g x 0.01g

81-2979

Moisture Content Tin

81-3000

Sample Container - Tinned Steel 0.5 litres

81-4030

Sample Tray - 406 x 406 x 50 mm

81-4020

Sample Tray - 306 x 306 x 38 mm

81-0590

Vernier Caliper (LCD) Range 0 to 200mm X 0.01mm

78-1250/01

225 Litre Drying Oven

81-0220

Aluminium Scoop Large

79-0020

200 mm Diameter Receiver

79-0010

200 mm Diameter Lid

79-0070

200mm Dia BS Sieve 63 Mic Stainless Steel Mesh.

79-0080

200mm Dia BS Sieve 75 Mic Stainless Steel Mesh.

79-0120

200mm Dia BS Sieve 150 Mic Stainless Steel Mesh.

79-0140

200mm Dia BS Sieve 212Mic Stainless Steel Mesh.

79-0160

200mm Dia BS Sieve 300Mic Stainless Steel Mesh.

79-0180

200mm Dia BS Sieve 425Mic Stainless Steel Mesh.

79-0200

200mm Dia BS Sieve 600Mic Stainless Steel Mesh.

79-0240

200mm Dia BS Sieve 1.18mm Stainless Steel Mesh.

79-0270

200mm Dia BS Sieve 2.00mm Stainless Steel Mesh.

79-2280

300mm Dia BS Sieve 2.36mm Stainless Steel Mesh.

79-2300

300mm Dia BS Sieve 3.35mm Stainless Steel Mesh.

79-2515

300mm Dia BS Sieve 5.00mm Perforated Plate.

79-2555

300mm Dia BS Sieve 10.0mm Perforated Plate.

79-2575

300mm Dia BS Sieve 14.0mm Perforated Plate.

79-2595

300mm Dia BS Sieve 20.0mm Perforated Plate.

79-2615

300mm Dia BS Sieve 28.0mm Perforated Plate.

79-2640

300mm Dia BS Sieve 37.5mm Perforated Plate.

79-2655

300mm Dia BS Sieve 50.0mm Perforated Plate.

79-2670

300mm Dia BS Sieve 63.0mm Perforated Plate.

79-2680

300mm Dia BS Sieve 75.0mm Perforated Plate.

79-2010

300mm Dia Lid.

79-2020

300mm Dia Receiver.

78-5477/01

Electronic Balance - 16 000 g x 0.5 g

79-7200

Sieve Brush Brass and Nylon

79-3515

450mm Dia BS Sieve 5 mm Stainless Steel Sieve. Perforated

79-3270

450mm Dia BS Sieve 2 mm Stainless Steel Mesh. Fitted with Reinforcing Mesh.

81-5100

Rubber Bucket

24-4145

Sodium Hexametaphosphate 500G.

78-5527/01

Electronic Balance - 32 000 g x 1.0 g

78-5485/01

Electronic Balance - 22000 g x 0.1 g

80-0200/01

ELE Sieve Shaker

82-5310

Maximum and Minimum Thermometer

29-4220

Contents

www.ele.com
+44 (0) 01525 249 200



200mm Calibrating Container 200mm Id X 250mm deep with a 350mm dia rim.

29-4200

200mm Sand Pouring Cylinder.

82-7401

Standard Sand - 600/300 µm

29-4340

Density Plate for EL29-4300.

81-0310

Trowel - Gardeners type



Dial Thermometer

Code: [78-1245](#)

Product Group: [N/A](#)

Standards

BS 1377

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Electronic Balance - 3600g x 0.01g

Code: [78-5447/01](#)

Product Group: [Electronic Balances](#)

Further Information

****Not available for sale in the USA****

Specification

Capacity resolution	3600 g x 0.01 g
Pan size	160 x 160 mm
Mains and battery	No
Dimensions (l x w x h)	260 x 170 x 90 mm
Weight	6 kg
Weighing units	g, kg, ct, GN, N, lb, oz, lb:oz, ozt, dwt, T, custom unit
Readability	0.1 g



Moisture Content Tin

Code: [81-2979](#)

Product Group: [Moisture Content Tin and Sample Containers](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****




Sample Container - Tinned Steel 0.5 litres

Code: [81-3000](#)

Product Group: [Moisture Content Tin and Sample Containers](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****




Sample Tray - 406 x 406 x 50 mm

Code: [81-4030](#)

Product Group: [Sample Trays](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Sample Tray - 306 x 306 x 38 mm

Code: [81-4020](#)

Product Group: [Sample Trays](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Vernier Caliper (LCD) Range 0 to 200mm X 0.01mm

Code: [81-0590](#)

Product Group: [Determination of the Shape Index,](#)
[Miscellaneous Laboratory Hardware](#)

Dual measuring range highly accurate vernier caliper 0 to 200mm x 0.01mm (8 inch x 0.001 inch) to comply with bs 887 and bs 6365. Complete with liquid crystal display.

Standards

EN 933-4

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****

Accessories



Vibrating Hammer

Code: [47-0455/01](#)

Alternatives



Vibrating Hammer

Code: [47-0455/01](#)



225 Litre Drying Oven

Code: [78-1250/01](#)

Product Group: [Percentage Refusal Density \(PRD\)](#),
[Oven Drying Method](#), [Oven Drying Method](#), [Oven Drying Method](#)

Standards

EN 12697-32, EN 13280-4, BS 598-104, BS 1377

Specification

Capacity	225 litres
External Dimensions (l x w x h)	540 x 1040 x 940
Internal Dimensions (l x w x h)	440 x 920 x 600
Fluctuation	± 0.75°C
Rated power heater elements	2000 W
Shelves supplied	3
Shelf positions	4
Weight	80 kg

Alternatives



100 Litre Drying Oven

Code: [78-1225/01](#)



150 Litre Drying Oven

Code: [78-1235/01](#)



425 Litre Drying Oven

Code: [78-0135/01](#)



50 Litre Drying Oven

Code: [78-1215/01](#)



Aluminium Scoop Large

Code: [81-0220](#)

Product Group: [Slump Test, Scoops and Shovels](#)

Further Information

****Not available for sale in the USA****



200 mm Diameter Receiver

Code: 79-0020

Product Group: Sieve Lids and Receivers ISO and BS, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200 mm Diameter Lid

Code: 79-0010

Product Group: Sieve Lids and Receivers ISO and BS, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 63 Mic Stainless Steel Mesh.

Code: [79-0070](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 75 Mic Stainless Steel Mesh.

Code: [79-0080](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 150 Mic Stainless Steel Mesh.

Code: [79-0120](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 212Mic Stainless Steel Mesh.

Code: 79-0140

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 300Mic Stainless Steel Mesh.

Code: 79-0160

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 425Mic Stainless Steel Mesh.

Code: 79-0180

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 600Mic Stainless Steel Mesh.

Code: 79-0200

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 1.18mm Stainless Steel Mesh.

Code: [79-0240](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 2.00mm Stainless Steel Mesh.

Code: [79-0270](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 2.36mm Stainless Steel Mesh.

Code: 79-2280

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 3.35mm Stainless Steel Mesh.

Code: 79-2300

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

NOT AVAILABLE FOR SALE IN THE USA



300mm Dia BS Sieve 5.00mm Perforated Plate.

Code: 79-2515

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 10.0mm Perforated Plate.

Code: 79-2555

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



300mm Dia BS Sieve 14.0mm Perforated Plate.

Code: 79-2575

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



300mm Dia BS Sieve 20.0mm Perforated Plate.

Code: 79-2595

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



300mm Dia BS Sieve 28.0mm Perforated Plate.

Code: 79-2615

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 37.5mm Perforated Plate.

Code: 79-2640

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 50.0mm Perforated Plate.

Code: 79-2655

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia BS Sieve 63.0mm Perforated Plate.

Code: 79-2670

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



300mm Dia BS Sieve 75.0mm Perforated Plate.

Code: 79-2680

Product Group: 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia Lid.

Code: 79-2010

Product Group: Sieve Lids and Receivers ISO and BS, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



300mm Dia Receiver.

Code: 79-2020

Product Group: Sieve Lids and Receivers ISO and BS, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves, 300mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Electronic Balance - 16 000 g x 0.5 g

Code: [78-5477/01](#)

Product Group: [Electronic Balances](#)

Further Information

****Not available for sale in the USA****

Specification

Capacity resolution	16000 g x 0.5 g
Pan size	225 x 300 mm
Mains and battery	Yes
Dimensions (l x w x h)	340 x 320 125 mm
Weight	4 kg



Sieve Brush Brass and Nylon

Code: [79-7200](#)

Product Group: [Sieve Brushes](#)

Double-ended, brass and nylon bristle

Standards

ASTM E11

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



450mm Dia BS Sieve 5 mm Stainless Steel Sieve. Perforated

Code: [79-3515](#)

Product Group: [450mm Diameter BS Sieves](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



450mm Dia BS Sieve 2 mm Stainless Steel Mesh. Fitted with Reinforcing Mesh.

Code: [79-3270](#)

Product Group: [450mm Diameter BS Sieves](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Rubber Bucket

Code: [81-5100](#)

Product Group: [Miscellaneous Laboratory Hardware](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Sodium Hexametaphosphate 500G.

Code: [24-4145](#)

Product Group: [Sodium Hexametaphosphate,](#)
[Mechanical Analysis Stirrer](#)

Standards

ASTM D422, AASHTO T88, ASTM E100

Spares/Consumables



Solid Rubber Stopper

Code: [4699-0881](#)



Electronic Balance - 32 000 g x 1.0 g

Code: 78-5527/01

Product Group: [Electronic Balances](#)

Further Information

****Not available for sale in the USA****

Specification

Capacity resolution	32000 g x 1.0 g
Pan size	225 x 275 mm
Mains and battery	Yes
Dimensions (w x d x h)	315 x 355 x 110 mm
Weight	6 kg
Weighing units	g, kg, lb, lb:oz, oz
Repeatability	1 g
Power supply	230AC, 50/60Hz, 10 watts



Electronic Balance - 22000 g x 0.1 g

Code: [78-5485/01](#)

Product Group: [Electronic Balances](#)

Further Information

****Not available for sale in the USA****

Specification

Capacity resolution	22000 g x 0.1 g
Pan size	400 x 300 mm
Mains and battery	Yes
Dimensions (w x d x h)	450 x 515 x 195 mm
Weight	7.6 kg
Weighing units	g, kg, ct, GN, N, lb, oz, lb:oz.



ELE Sieve Shaker

Code: [80-0200/01](#)

Product Group: [ELE Sieve Shaker](#)

The ELE sieve shaker is powered by an electromagnetic drive that has no rotating parts to wear making it maintenance free and extremely quiet in operation.

The unit features a triple Vertical-Lateral-Rotary vibrating action that moves the sample over the sieve producing faster more efficient sieving, while the rapid vertical movements also help keep the apertures from blinding.

The shaker is ideal for laboratory or on site use. It is robust, compact and sufficiently lightweight to be portable. The separate digital microprocessor controlled console unit incorporates a keypad for setting the sieving program and is isolated from any effects of vibration from the shaker.

As standard the shaker includes, timer 0-999 minutes, adjustable vibration intensity and adjustable intermittent or continuous operation.

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****

The unit accepts up to ten 200 mm or 8 inch, full height, diameter sieves and lid and receiver, or up to six 300 mm or 12 inch diameter sieves and lid and receiver. Complete as specified. Dimensions (l x w x h) 380 x 440 x 1085 mm. For 220 - 240 V AC, 50 Hz 1ph.



Maximum and Minimum Thermometer

Code: [82-5310](#)

Product Group: [General-purpose Thermometers](#)

Non hazardous. Range -40 - +50°C

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Calibrating Container 200mm Id X 250mm deep with a 350mm dia rim.

Code: [29-4220](#)

Product Group: [Sand Replacement](#)

Standards

BS 1377, BS 1924



200mm Sand Pouring Cylinder.

Code: [29-4200](#)

Product Group: [Sand Replacement](#)

Standards

BS 1377, BS 1924



Standard Sand - 600/300 μ m

Code: [82-7401](#)

Product Group: [Sand Cone 6"](#), [Chemicals](#), [Test and Reference Materials](#)

Fraction C. No hazard. 20 kg.

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****

Accessories



Density Plate for EL29-4300.

Code: [29-4340](#)

Alternatives



Density Plate for EL29-4300.

Code: [29-4340](#)



Density Plate for EL29-4300.

Code: [29-4340](#)

Product Group: [Sand Cone 6"](#)

For 6 inch sand cone. The plate has a 6.5 inch diameter recessed hole to locate the sand cone.

Standards

ASTM D1556, AASHTO T191

Accessories



Standard Sand - 600/300 μm

Code: [82-7401](#)

Alternatives



Standard Sand - 600/300 μm

Code: [82-7401](#)



Trowel - Gardeners type

Code: [81-0310](#)

Product Group: [Trowels and Floats](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****