



IF IT'S WORTH BUILDING, IT'S WORTH TESTING

This wishlist was generated on 19/10/2018, and contains the following Products:

79-0020

200 mm Diameter Receiver

79-0040

200mm Dia BS Sieve 38 Mic Stainless Steel Mesh.

79-0050

200mm Dia BS Sieve 45 Mic Stainless Steel Mesh.

79-0060

200mm Dia BS Sieve 53 Mic Stainless Steel Mesh.

79-0070

200mm Dia BS Sieve 63 Mic Stainless Steel Mesh.

79-0080

200mm Dia BS Sieve 75 Mic Stainless Steel Mesh.

79-0085

200mm Dia Iso:565 3310/1 Sieve 80 Mic Stainless Steel Mesh.

79-0090

200mm Dia BS Sieve 90 Mic Stainless Steel Mesh.

79-0095

200mm Dia Iso:565 3310/1 Sieve 100 Mic Stainless Steel Mesh.

79-0100

200mm Dia BS Sieve 106Mic Stainless Steel Mesh.

79-0110

200mm Dia BS Sieve 125Mic Stainless Steel Mesh.

79-0120

200mm Dia BS Sieve 150 Mic Stainless Steel Mesh.

79-0125

200mm Dia Iso:565 3310/1 Sieve 160 Mic Stainless Steel Mesh.

79-0130

200mm Dia Iso:565 3310/1 Sieve 180 Mic Stainless Steel Mesh.

79-0135

200mm Dia Iso:565 3310/1 Sieve 200 Mic Stainless Steel Mesh.

79-0140

200mm Dia BS Sieve 212Mic Stainless Steel Mesh.

79-0150

200mm Dia BS Sieve 250Mic Stainless Steel Mesh.

79-0160

200mm Dia BS Sieve 300Mic Stainless Steel Mesh.

79-0170

200mm Dia Iso:565 3310/1 Sieve 355 Mic Stainless Steel Mesh.

79-0175

200mm Dia Iso:565 3310/1 Sieve 400 Mic Stainless Steel Mesh.

79-0180

200mm Dia BS Sieve 425Mic Stainless Steel Mesh.

79-0210

200mm Dia BS Sieve 710Mic Stainless Steel Mesh.

79-0200

200mm Dia BS Sieve 600Mic Stainless Steel Mesh.

79-0220

200mm Dia BS Sieve 850Mic Stainless Steel Mesh.

79-0230

200mm Dia BS Sieve 1.00mm Stainless Steel Mesh.

79-0240

200mm Dia BS Sieve 1.18mm Stainless Steel Mesh.

79-0245

200mm Dia Iso:565 3310/1 Sieve 1.25mm Stainless Steel Mesh.

79-0250

200mm Dia BS Sieve 1.40mm Stainless Steel Mesh.

79-0255

200mm Dia Iso:565 3310/1 Sieve 1.60mm Stainless Steel Mesh.

79-0260

200mm Dia BS Sieve 1.70mm Stainless Steel Mesh.

79-0270

200mm Dia BS Sieve 2.00mm Stainless Steel Mesh.

79-0280

200mm Dia BS Sieve 2.36mm Stainless Steel Mesh.

79-0285

200mm Dia Iso:565 3310/1 Sieve 2.50mm Stainless Steel Mesh.

79-0290

200mm Dia BS Sieve 2.80mm Stainless Steel Mesh.

79-0300

200mm Dia BS Sieve 3.35mm Stainless Steel Mesh.

79-0310

200mm Dia BS Sieve 4.00mm Stainless Steel Mesh.

79-0320

200mm Dia BS Sieve 4.75mm Stainless Steel Mesh.

79-0340

200mm Dia BS Sieve 6.7mm Stainless Steel Mesh

79-0010

200 mm Diameter Lid

25-0402

Consolidation Frame One Dimensional Consolidation Incremental Loading Device.

25-0408

Set of Weights 100Kg Total Weight.

25-0429

Floor Mounting Stand.

25-0503

Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Contents

www.ele.com
+44 (0) 01525 249 200



25-0506

Cutting Ring 75mm Cell.

25-0503/13

75mm Dia Upper and Lower Porous Stones for Use on EL25-0503 Series Cell.

25-0509

Calibration Disc 75mm Cell

25-0440

Dial Gauge 10mm Travel X 0.002mm Divisions.

26-2261

Pocket Shearmeter with 3 Vanes 0 to 1Kgf/Cm2 X 0.5Kgf/Cm2.



200 mm Diameter Receiver

Code: 79-0020

Product Group: Sieve Lids and Receivers ISO and BS, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 38 Mic Stainless Steel Mesh.

Code: [79-0040](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

200mm Diameter 38 Microns Aperture Brass Framed Sieve With Stainless Steel Mesh To BS 410

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 45 Mic Stainless Steel Mesh.

Code: 79-0050

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 53 Mic Stainless Steel Mesh.

Code: 79-0060

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 63 Mic Stainless Steel Mesh.

Code: 79-0070

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 75 Mic Stainless Steel Mesh.

Code: [79-0080](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 80 Mic Stainless Steel Mesh.

Code: 79-0085

Product Group: 200mm Diameter BS Sieves, 200mm
Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 90 Mic Stainless Steel Mesh.

Code: [79-0090](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 100 Mic Stainless Steel Mesh.

Code: 79-0095

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 106Mic Stainless Steel Mesh.

Code: 79-0100

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 125Mic Stainless Steel Mesh.

Code: [79-0110](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 150 Mic Stainless Steel Mesh.

Code: [79-0120](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 160 Mic Stainless Steel Mesh.

Code: 79-0125

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 180 Mic Stainless Steel Mesh.

Code: 79-0130

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS410-1, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 200 Mic Stainless Steel Mesh.

Code: 79-0135

Product Group: 200mm Diameter BS Sieves, 200mm
Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

ISO 565, EN933-2, BS410-1

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 212Mic Stainless Steel Mesh.

Code: 79-0140

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 250Mic Stainless Steel Mesh.

Code: 79-0150

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 300Mic Stainless Steel Mesh.

Code: 79-0160

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 355 Mic Stainless Steel Mesh.

Code: 79-0170

Product Group: 200mm Diameter BS Sieves, 200mm
Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS410-1, EN933-2, ISO 3310-1, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 400 Mic Stainless Steel Mesh.

Code: 79-0175

Product Group: 200mm Diameter BS Sieves, 200mm
Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 425Mic Stainless Steel Mesh.

Code: [79-0180](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 710Mic Stainless Steel Mesh.

Code: 79-0210

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 600Mic Stainless Steel Mesh.

Code: 79-0200

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 850Mic Stainless Steel Mesh.

Code: 79-0220

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 1.00mm Stainless Steel Mesh.

Code: 79-0230

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 1.18mm Stainless Steel Mesh.

Code: 79-0240

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 1.25mm Stainless Steel Mesh.

Code: 79-0245

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 1.40mm Stainless Steel Mesh.

Code: 79-0250

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia Iso:565 3310/1 Sieve 1.60mm Stainless Steel Mesh.

Code: 79-0255

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 1.70mm Stainless Steel Mesh.

Code: 79-0260

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 2.00mm Stainless Steel Mesh.

Code: [79-0270](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 2.36mm Stainless Steel Mesh.

Code: [79-0280](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia Iso:565 3310/1 Sieve 2.50mm Stainless Steel Mesh.

Code: 79-0285

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 2.80mm Stainless Steel Mesh.

Code: 79-0290

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 3.35mm Stainless Steel Mesh.

Code: 79-0300

Product Group: 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

NOT AVAILABLE FOR SALE IN THE USA



200mm Dia BS Sieve 4.00mm Stainless Steel Mesh.

Code: [79-0310](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, EN933-2, ISO 565

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 4.75mm Stainless Steel Mesh.

Code: [79-0320](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Standards

BS 410-1, ISO 3310, ISO 565, EN933-2

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200mm Dia BS Sieve 6.7mm Stainless Steel Mesh

Code: [79-0340](#)

Product Group: [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#), [200mm Diameter BS Sieves](#)

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



200 mm Diameter Lid

Code: 79-0010

Product Group: Sieve Lids and Receivers ISO and BS, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves, 200mm Diameter BS Sieves

Standards

BS 410-1, ISO 3310

Further Information

****NOT AVAILABLE FOR SALE IN THE USA****



Consolidation Frame One Dimensional Consolidation Incremental Loading Device.

Code: 25-0402

Product Group: Consolidation Apparatus, Table Top Consolidation Apparatus

- High capacity - 8800 kPa on 50 mm diameter specimens using 11:1 beam ratio
- Triple beam ratio, 9:1, 10:1, 11:1
- Compact unit ensures maximum space saving

The ELE Oedometer is rigidly constructed to ensure minimum frame distortion. The frame is designed to load the specimen through a yoke assembly and one of three alternative beam ratios. The beam is fitted with a counterbalance weight and beam support jack. The cell platform will accept the complete range of ELE consolidation cells and is fitted with a central spigot to ensure accurate centring of the cell under the loading yoke. Dimensions without hanger 711 x 203 x 508 mm (l x w x h). Weight 24 kg.

Standards

ASTM D2435, ASTM D4546, AASHTO T216, ASTM D3877, BS 1377-5

Further Information

Supplied without dial gauge and weights.

Specification

Load Capacity	48 tons/sq. ft. (5,14 8 kPa) on 2.5" (63 mm) diam. samples.
Loading Beam	Cast aluminum; counterbalanced; 9:1,10:1 and 11 :1 ratios.
Frame	Cast aluminum; integral beam support jack; plated steel and platform.
Dimensions	203 x 711 x 508 mm, (8" w. x 28" d. x 20" h) . excluding weight hanger.
Weight	24 KG

Accessories



16 Ton Weight Set

Code: [25-0544](#)



2.416" Fixed Ring Consolidometer

Code: [25-0480](#)



2.5" Floating Ring Consolidometer

Code: [25-0530](#)



Consolidation Cell Complete 2.5 Inch Diameter Sample. Inc. Porous Discs and Cutting Ring.

Code: [25-0479](#)



Consolidation Cell Complete 50mm Diameter Sample.

Code: [25-0455](#)



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: [25-0503](#)



Floor Mounting Stand.

Code: [25-0429](#)



Mechanical Dial Indicator - 0.4" Range

Code: [88-4070](#)



Mechanical Dial Indicator - 1.0" Range Counter Clockwise Movement

Code: [88-4120](#)



Mechanical Dial Indicator - 10 mm Range

Code: [88-4080](#)



Mechanical Dial Indicator - 25 mm Range Counter Clockwise Movement

Code: [88-4130](#)



Set of Weights 100Kg Total Weight.

Code: [25-0408](#)



Weight Set A

Code: [25-0535](#)



Weight Set B

Code: [25-0537](#)


Spares/Consumables



Electronic Digital Indicator, 0.600"/15 mm range

Code: [88-4210](#)

Alternatives



Pneumatic Consolidation Apparatus

Code: [25-0560](#)



Set of Weights 100Kg Total Weight.

Code: [25-0408](#)

Product Group: [Consolidation Apparatus](#)

9 x 10 kg, 1 x 5 kg, 2 x 2 kg, 1 x 1 kg.

Standards

ASTM D2435, ASTM D4546, AASHTO T216, ASTM D3877, BS 1377-5



Floor Mounting Stand.

Code: [25-0429](#)

Product Group: [Consolidation Apparatus, Table Top Consolidation Apparatus](#)

A versatile modular steel stand. Holes in the shelf are provided for securing up to three EL25-0402 Consolidation Frames. Dimensions 610 x 915 x 865 mm (l x w x h).

Standards

ASTM D2435, ASTM D4546, AASHTO T216, ASTM D3877, BS 1377-5



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: 25-0503

Product Group: Table Top Consolidation Apparatus, BS EN consolidation cells and accessories, Pneumatic Consolidation Apparatus, Fixed Ring Consolidation

Specification

Application	BS/EN 10:1
Specimen Dia	75 mm
Specimen area	4418 mm ²
Beam ratio	9:1
Load kg	1
Stress	20 kPa
Typical max stress	3.2 MPa
Stress for 1 kg m ²	20 kPa
Application	BS
Specimen Diameter	75 mm
Specimen Area	4418 mm ²
Beam Ratio	10:01
Load	1 kg
Stress	20 kPa
Typical Maximum Stress	3.2 MPa
Stress for 1 kg	20 kPa

Accessories



Calibration Disc 75mm Cell

Code: 25-0509



Consolidation Cell Complete 2.5 Inch Diameter Sample. Inc. Porous Discs and Cutting Ring.

Code: 25-0479



Consolidation Cell Complete 50mm Diameter Sample.

Code: [25-0455](#)

Spares/Consumables



75mm Dia Upper and Lower Porous Stones for Use on EL25-0503 Series Cell.

Code: [25-0503/13](#)



Cutting Ring 75mm Cell.

Code: [25-0506](#)

Alternatives



Calibration Disc 75mm Cell

Code: [25-0509](#)



Consolidation Cell Complete 2.5 Inch Diameter Sample. Inc. Porous Discs and Cutting Ring.

Code: [25-0479](#)



Consolidation Cell Complete 50mm Diameter Sample.

Code: [25-0455](#)



Cutting Ring 75mm Cell.

Code: [25-0506](#)

Product Group: [BS EN consolidation cells and accessories](#), [Fixed Ring Consolidation](#)

Standards

BS 1377-5

Accessories



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: [25-0503](#)



75mm Dia Upper and Lower Porous Stones for Use on EL25-0503 Series Cell.

Code: [25-0503/13](#)

Product Group: [BS EN consolidation cells and accessories](#), [Fixed Ring Consolidation](#)

Standards

BS 1377-5

Accessories



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: [25-0503](#)



Calibration Disc 75mm Cell

Code: [25-0509](#)

Product Group: [BS EN consolidation cells and accessories](#), [Fixed Ring Consolidation](#)

Standards

BS 1377-5

Accessories



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: [25-0503](#)

Alternatives



Consolidation Cell/ Oedometer Complete 75mm Diameter Sample

Code: [25-0503](#)



Dial Gauge 10mm Travel X 0.002mm Divisions.

Code: [25-0440](#)

Product Group: [Measurement of Horizontal and Vertical Movement](#), [Vertical settlement measurement](#), [Direct/Residual Shear Apparatus](#)

Spares/Consumables



Electronic Digital Indicator, 0.600"/15 mm range

Code: [88-4210](#)



Vertical Dial Indicator, English

Code: [25-0445](#)



Pocket Shearmeter with 3 Vanes 0 to 1Kgf/Cm2 X 0.5Kgf/Cm2.

Code: [26-2261](#)

Product Group: [Torvane Shear Device, Pocket Shearmeter](#)

The shearmeter can be used on tube samples, on the sides of pits, cuttings etc. It is an invaluable tool for initial site investigation work.

Further Information

Complete with sensitive vane, standard vane and high-capacity vane. Range 0 to 1 x 0.05 kgf/cm2.

Specification

Vane Driver	1.6" (41 mm) diam. x 3.2" (81 mm) l. with vane attached.
Dial Scale	1 kg/sq. cm (tons/sq. ft.) x 0.05 subdivisions.
Carrying Case	Plastic; 6" w. x 4" d. x 2" h. (152 x 102 x 51 mm).
Weight	Net 10.5 oz. (300 g).

Spares/Consumables



High-Capacity Vane

Code: [26-2261/14](#)



Sensitive Vane

Code: [26-2261/10](#)



Standard Vane

Code: [26-2261/12](#)

Alternatives



Digital Direct/Residual Shear Apparatus Complete with Lever Loading Assembly. 110-120V 50/60Hz 1Ph.

Code: [26-2114/02](#)



Digital Direct/Residual Shear Apparatus Complete with Lever Loading Assembly. 220-240V 50/60Hz 1Ph.

Code: [26-2114/01](#)



Hand Vane Tester

Code: [26-3346](#)