

















IF IT'S WORTH BUILDING, IT'S WORTH TESTING

Contents





This wishlist was generated on 20/03/2019, and contains the following Products:

24-2830

Gas Jar 75mm Dia X 300mm with Glass Cover and Rubber Bung.

34-4570

150mm Cube Mould 4-Part Clamp Type. Cast Iron Construction. BS EN Compliant.

36-3320/01

ADR Touch SOLO 3000 BS EN Compression Machine with Digital Readout and **Self Centring Platens.**

6014A0062

Pressure transducer, 0-700bar, 0.05 to 10v DC Output

78-1235/01

150 Litre Drying Oven





Gas Jar 75mm Dia X 300mm with Glass Cover and Rubber Bung.

Code: 24-2830

Product Group: Gas Jar Method

1 litre capacity complete withrubber bung and glass cover.

StandardsBS 1377, EN 1997-2

Accessories



Mechanical End-Over-End Shaker Ce

Code: 24-2854/01

www.ele.com 🚆 +44 (0)1525 249 200 💻 +1 (800) 323 1242

Page 3 of 11







150mm Cube Mould 4-Part Clamp Type. Cast Iron Construction. BS EN Compliant.

Code: 34-4570

Product Group: Cube Moulds, Cube Moulds

4-part with clamp attached base plate.

Standards

BS 1881-108, EN 12390-1, EN 12390-2

Specification

Construction Bolted sides and clamped base

plate

Finish Painted

Weight 42 lb (19.1 kg)

Accessories



Aluminium Scoop Large

Code: 81-0220



Compacting Bar 25mm Sq X 380mm

Code: 34-2910



Float - Plasterer's type

Code: 81-0340

www.ele.com # +44 (0)1525 249 200 # +1 (800) 323 1242 Page 4 of 11







Mould Oil (25 Litre Drum)

Code: 82-7341



Wire Brush

Code: 81-0705

Spares/Consumables



Soft Headed Mallet.

Code: 29-5020

Alternatives



Vibrating Table 600 X 400mm Table Top. 220-240V 50Hz 1Ph. Supplied with clamping assembly

Code: 34-6250/01

www.ele.com +44 (0)1525 249 200

= +1 (800) 323 1242







ADR Touch SOLO 3000 BS EN Compression Machine with Digital Readout and Self Centring Platens.

Code: 36-3320/01

Product Group: BS EN Compression Machines

The ADR Touch range of 2000 kN and 3000 kN capacity compression machines has been designed to meet the need for reliable and consistent testing. The load frame is a welded steel fabrication carrying the ball-seated upper platen. Positively located on the loading ram, which is protected from debris by a flexible cover, the lower platen is marked for the centring of cube and cylinder specimens. Self-centring lower platens for cube location are supplied as standard on EN machines and are available as an optional extra on the standard machine. The two machines for cube testing to EN standards are assembled and aligned using a special compression

assembled and aligned using a special compression frame stability tester.

The dimensions of the frame allow the testing of concrete cylinders up to 320 mm long x 160 mm diameter, 150 and 100 mm square cubes, and on EN/BS machines, 200 mm square cubes. Kerbs and flagstones may also be tested on ADR machines as well as 150 mm and 100 mm square section beams to ASTM C78 using the optional 100 kN flexural frames which are connected to the power pack.

Standards

EN 12350-6, NF P18-411

Further Information

Not available for sale in the USA

ADR Touch BS EN 2000 and 3000 kN compression machines are supplied complete with self-centring lower platen and safety gates fitted with interlock switches ready for testing 300×150 mm diameter cylinders.

Whilst delivering all the features and reputation of the established ADR Series with its extensive design history, the new and improved user interface provides a high quality platform for testing that enhances the performance of ELE's compression machines.

New, sophisticated electronics further the benefits of simplified operation, whilst delivering the highest levels of accuracy in testing concrete and cement/mortar samples, satisfying the needs of Quality Control Managers, Lab Managers and Technicians.

ACCURACY & SAVINGS

The new ADR Touch Series, with 145mm (5.7") high resolution QVGA touch screen interface and intuitive menu-driven operation, reduces the time taken to set up the machine and perform tests, reducing the time to train staff by up to 25%.



- Up to 6 sample types can be set as favorites, enabling one-touch set up for repeat testing.
- Full, QWERTY touch pad for input of test data.

Most testing errors produce lower strength results. Noncompliant loading rates can generate errors in measured strength. The user interface includes real-time display of load vs. time, further ensuring accurate and consistent test results and providing "goodness of test" data to improve traceability in your QC operations.

TRACEABILITY & DATA QUALITY

The ADR range now provides improved data quality and traceability in due diligence cases - it is now possible to demonstrate traceability all the way from the machine/user to the accreditation body, increasing your reputation and peace of mind - all test results now come complete with the machine serial number attached.

- Enhanced USB data communications between PC and machine eliminating the need for download software.
- Two gigabytes of storage memory.
- Full customization of sample sizes stress calculations are automatically recalculated.

USER SAFETY

With full safety gates as standard, total systems diagnostics, ram run-out switches and overload warnings ensure the

safety of your employees and the reliability of your machine.

Specification

Testing Standards BS EN 12390-4, BS EN

12390-3, BS EN 12390-4, BS EN 12390-5, EN 12504-1, EN 1354, EN 1521, EN 3161, EN 1338, EN 772-6, EN 13286-41, BS 3892-3, BS 187, BS 6717, BS EN ISO 7500-1, ASTM E4

Capacity 3000 kN
Cubes (Concrete) Up to 200 mm
Cylinders (Concrete) Up to 160 x 320 mm

Blocks Via optional Platen Handling

System

Flexural Testing Via Flexural Frame

TFV and ACV Yes

Voltage Supply 220-240V 50/60 Hz 1Ph.

Frame Class (Stability)

Frame Type

Max vert. Clearance

Max hor. Clearance

310 mm

Platen Sizes Lower 220mm sq,

Upper 300mm dia

Max Ram Travel 50 mm

Accessories

www.ele.com # +44 (0)1525 249 200 # +1 (800) 323 1242 Page 7 of 11



Page 8 of 11



100kN Flexural Fitting Kit (ADR) Used for Connecting Flexural Frames to ADR Compression Machines.

Code: 37-6138



3000 kN Load Calibration Device Complete with Hand Held **Readout Unit ISO376**

Code: 37-8400



ADR Touch Head for Compression Machines

Code: 37-5951/09



BS/EN Standard Rectangular Platen

Code: 37-4860



EN 12390-3/4 Distance Piece - 100 mm Depth

Code: 37-5180

+44 (0)1525 249 200 **= +1 (800) 323 1242**





Page 9 of 11




EN 12390-3/4 Distance Piece - 20 mm Depth

Code: 37-5110



EN 12390-3/4 Distance Piece - 50 mm Depth

Code: 37-5120



EN 12390-3/4 Distance Piece - 60 mm Depth

Code: 37-5140



Impact Printer Rs232 Serial Connection. Supplied Complete with 1 Paper Roll.

Code: 37-4859/01

Spares/Consumables



Pressure transducer, 0-700bar, 0.05 to 10v DC Output

Code: 6014A0062



Pressure transducer, 0-70bar, 0.05 to 10v DC Output

Code: 6014A0065

www.ele.com +44 (0)1525 249 200 = +1 (800) 323 1242





Pressure transducer, 0-700bar, 0.05 to 10v DC Output

Code: 6014A0062

Product Group: Spares, Softwares

Further Information

Not available for sale in the USA

www.ele.com # +44 (0)1525 249 200 # +1 (800) 323 1242 Page 10 of 11







150 Litre Drying Oven

Code: 78-1235/01

Product Group: Oven Drying Method, Oven Drying

Method, Oven Drying Method

Standards

BS 2648, BS 598, BS 1377, BS 1924

Further Information

NOT AVAILABLE FOR SALE IN THE USA

Alternatives



100 Litre Drying Oven

Code: 78-1225/01



225 Litre Drying Oven

Code: 78-1250/01



50 Litre Drying Oven

Code: 78-1215/01



Drying Oven 425 Litre Capacity

Code: 78-0135/01

www.ele.com # +44 (0)1525 249 200 # +1 (800) 323 1242 Page 11 of 11